



## Eaton N201-010-GY

Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), Gray, 10 ft. (3.05 m)



<b>PRODUCT NAME</b>	Eaton Tripp Lite series preterminated copper patch cables
<b>CATALOG NUMBER</b>	N201-010-GY
<b>UPC</b>	037332099952
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	9 in
<b>PRODUCT WIDTH</b>	7 in
<b>PRODUCT WEIGHT</b>	0.26 lb
<b>COMPLIANCES</b>	RoHS REACH IEEE Certified
<b>CERTIFICATIONS</b>	UL Listed cUL Listed



Powering Business Worldwide

<b>SPECIAL FEATURES</b>	0% to 90% RH, Non-Condensing
<b>CABLE JACKET RATING</b>	CM
<b>CABLE JACKET COLOR</b>	Gray
<b>PACKAGE CONTENTS</b>	10-ft. (3.05 m) Cat6 Gray Gigabit Patch Cord Snagless Molded
<b>SYSTEM REQUIREMENTS</b>	PoE Cat6 For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.
<b>IEEE STANDARDS SUPPORTED</b>	802.3at 802.3an
<b>CONNECTOR TYPE</b>	Networking-copper
<b>PRODUCT FEATURES</b>	Snagless Connector PoE Support
<b>CABLE JACKET MATERIAL</b>	PVC
<b>NETWORK SPEED</b>	1 Gbps (Gigabit)
<b>PRODUCT HIGHLIGHTS</b>	Premium cabling for Category 6, Category 5e and Category 5 applications—rated for 550 MHz/1 Gbps communications All cables feature boots with integral strain-relief and RJ45 (Male) connectors Designed to meet Category 6 specifications; reduces cross-talk and return loss IEEE 802.3ab PVC 4-pair stranded UTP
<b>CONTACT PLATING</b>	Gold
<b>SIDE A CONNECTOR1</b>	RJ45 (MALE)
<b>SIDE B CONNECTOR1</b>	RJ45 (MALE)
<b>SIDE B CONNECTOR3</b>	RJ45 (MALE)
<b>TECHNOLOGY</b>	Cat6
<b>OPERATING HUMIDITY</b>	0% to 90% RH, Non-Condensing
<b>OPERATING TEMPERATURE RANGE</b>	14° to 122°F (-10° to 50°C)
<b>STORAGE HUMIDITY</b>	0% to 90% RH, Non-

