



Eaton N201-S03-BL

Cat6 Gigabit Snagless Slim UTP Ethernet Cable (RJ45 M/M), Blue, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N201-S03-BL
UPC	037332193056
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.05 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

□□□□	
SPECIAL FEATURES	5% to 85% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	N201-S03-BL Cat6 Gigabit Snagless Slim UTP Patch Cable (RJ45 M/M), 3 ft.
SYSTEM REQUIREMENTS	Cat6
IEEE STANDARDS SUPPORTED	802.3at 802.3ab 802.3af
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	High-quality 28 AWG copper wire Lifetime limited warranty (Worldwide) Snagless RJ45 male connectors Easy to route through cable management panels Rated for Cat6 Gigabit/1 Gbps communications Over 38% slimmer than standard Cat6 cables
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	5% to 85% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
CONDUCTOR GAUGE	28 AWG
CABLE LENGTH	3 Foot
OUTER CABLE DIAMETER	3.8 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
BANDWIDTH PER TIA	250 MHz

STANDARD	
MAXIMUM BANDWIDTH AS TESTED	550 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at) Type 1 PoE (15.4W, IEEE 802.3af)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Slim
CABLE STYLE	Snagless
