



Eaton N201-S05-BL

Cat6 Gigabit Snagless Slim UTP Ethernet Cable (RJ45 M/M), Blue, 5 ft. (1.52 m) (N201-S05-BL)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N201-S05-BL
UPC	037332193070
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.07 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

□□□□	
SPECIAL FEATURES	5% to 85% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	N201-S05-BL Cat6 Gigabit Snagless Slim UTP Patch Cable (RJ45 M/M), 5 ft.
SYSTEM REQUIREMENTS	Cat6
IEEE STANDARDS SUPPORTED	802.3ab 802.3af 802.3at
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Over 38% slimmer than standard Cat6 cables High-quality 28 AWG copper wire Snagless RJ45 male connectors Easy to route through cable management panels Rated for Cat6 Gigabit/1 Gbps communications
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	5% to 85% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
CONDUCTOR GAUGE	28 AWG
CABLE LENGTH	5 Foot
OUTER CABLE DIAMETER	3.8 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
BANDWIDTH PER TIA	250 MHz

□□

STANDARD	
MAXIMUM BANDWIDTH AS TESTED	550 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 1 PoE (15.4W, IEEE 802.3af) Type 2 PoE+ (30W, IEEE 802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Slim
CABLE STYLE	Snagless
