



Eaton N202-050-BL

Cat6 Gigabit Solid Conductor Snagless UTP Ethernet Cable (RJ45 M/M), Blue, 50 ft. (15.24 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N202-050-BL
UPC	037332157409
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	0.96 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS IEEE Certified
CERTIFICATIONS	cUL Listed UL Listed

□□□□		□□	
SPECIAL FEATURES	0% to 90% RH, Non-Condensing		
CABLE JACKET RATING	CM		
CABLE JACKET COLOR	Blue		
PACKAGE CONTENTS	N202-050-BL, 50-ft. (15.24 m) Blue Cat6 Solid Conductor Patch Cable		
SYSTEM REQUIREMENTS	Cat6 PoE		
IEEE STANDARDS SUPPORTED	802.3an 802.3at		
CONNECTOR TYPE	Networking-copper		
PRODUCT FEATURES	Snagless Connector PoE Support		
CABLE JACKET MATERIAL	PVC		
NETWORK SPEED	1 Gbps (Gigabit)		
PRODUCT HIGHLIGHTS	High-quality copper wire and a shortened body plug design Meets Category 6 cabling standards Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation Solid Conductor 4 Pair Cable for long distance patch runs Lifetime limited warranty (Worldwide) Drastically reduce impedance and structural return loss compared to Stranded Conductor patch cables		
CONTACT PLATING	Gold		
SIDEA CONNECTOR1	RJ45 (MALE)		
SIDEB CONNECTOR1	RJ45 (MALE)		
SIDEB CONNECTOR3	RJ45 (MALE)		
TECHNOLOGY	Cat6		
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing		
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)		
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing		
STORAGE TEMPERATURE	5° to 140°F (-15° to 60°C)		
CONDUCTOR GAUGE	24 AWG		

CABLE LENGTH	50 Foot
OUTER CABLE DIAMETER	6.0 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
BANDWIDTH PER TIA STANDARD	250 MHz
MAXIMUM BANDWIDTH AS TESTED	500 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	20 - 50ft (6 - 15M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Regular
CABLE STYLE	Solid Snagless
