



Eaton N205-006-BL-FCR

Cisco Console Rollover Cable (RJ45 M/M), 6 ft. (1.83 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N205-006-BL-FCR
UPC	037332194183
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.13 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS

□□□□

COLOR	Blue
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	N205-006-BL-FCR Cisco Console Rollover Cable (RJ45 M/M), 6 ft.
SYSTEM REQUIREMENTS	Cat6 Computer or laptop with RJ45 port Cisco networking hardware with RJ45 console port
CONNECTOR TYPE	Networking-copper
CABLE JACKET MATERIAL	PVC
PRODUCT HIGHLIGHTS	Rugged PVC jacket Lifetime limited warranty (Worldwide) Works with new and old Cisco equipment Direct replacement for existing Cisco rollover cable Male RJ45 connectors 32 AWG copper wire
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEA CONNECTOR2	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6
CONDUCTOR GAUGE	32 AWG
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	4 Pair
BANDWIDTH PER TIA STANDARD	250 MHz
DATA TRANSFER RATE	1 Gbps
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)

□□

