



Eaton N206-PC10-IND

Industrial Cat5e/Cat6 STP Ethernet Cable -
RJ45 M/M, CMX Outdoor, IP68, 26 AWG, TAA,
10 ft. (3.05 m)


□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated patch cable
CATALOG NUMBER	N206-PC10-IND
UPC	037332206305
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10.7 in
PRODUCT WIDTH	8 in
PRODUCT WEIGHT	0.39 lb
WARRANTY	Limited lifetime
COMPLIANCES	IEEE Certified REACH RoHS
CERTIFICATIONS	cUL Listed UL Listed



Powering Business Worldwide

□□□□	
SPECIAL FEATURES	20% to 80% RH, Non-Condensing
CABLE JACKET RATING	CMX
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	N206-PC10-IND Industrial Cat5e/Cat6 STP Patch Cable - RJ45 M/M, 10-ft. (3.05 m)
SYSTEM REQUIREMENTS	Cat5/5e Cat6 PoE
IEEE STANDARDS SUPPORTED	802.3at 802.3af
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	TAA Compliant Industrial Grade PoE Support
CABLE JACKET MATERIAL	PBT
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Complies with Federal Trade Agreements Act standards for GSA Schedule purchases IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.* Dispels EMI/RFI line noise that can destroy data and affect equipment performance Supports PoE to save you expense and effort of powering PoE devices individually Built to protect Gigabit Ethernet and digital signage applications in harsh environments Lifetime limited warranty (Worldwide) Standard IP68 rating is 1.5m / 30 minutes. Note: IP68 Rating of water resistance in depths up to 1.5 meters for 60 minutes is based on manufacturer's guarantee.
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)



TECHNOLOGY	Cat6 Cat5/5e
OPERATING HUMIDITY	20% to 80% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
STORAGE HUMIDITY RANGE	20% to 80% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 176°F (-20° to 80°C)
CONDUCTOR GAUGE	26 AWG
CABLE LENGTH	10 Foot
OUTER CABLE DIAMETER	6.2 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 176°F (-20° to 80°C)
CABLE SHIELDING	STP
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
TAA COMPLIANCE	Yes
CABLE SHEATH MATERIAL	STP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)

POE TYPE	Type 1 PoE (15.4W, IEEE 802.3af) Type 2 PoE+ (30W, IEEE 802.3at)
POWER OVER ETHERNET (POE)	15.4W (802.3af) 30W (802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Regular
CABLE STYLE	Outdoor Molded Industrial

