



Eaton N206-SB01-IND

Waterproof Electrical Junction Box - Surface Mount, Industrial, Single Gang, IP68, TAA, 2 Cutouts (N206-SB01-IND)

□□□□

PRODUCT NAME	Eaton Tripp Lite series electrical junction box
CATALOG NUMBER	N206-SB01-IND
UPC	037332206213
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10.7 in
PRODUCT WIDTH	8 in
PRODUCT WEIGHT	0.5 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	UL Listed

SPECIAL FEATURES

Important Note Additional tools may be required during installation when punching out cut-outs for M16 Cable Glands.

APPLICATION

- Connect Gigabit Ethernet networks, security cameras or digital signage in factories, warehouses, mills and other industrial environments
- Provide Cat6, USB 3.0 or 4K HDMI connectivity in outdoor environments susceptible to rain, such as a stadium or outdoor arena
- Set up outdoor digital signage at malls, theaters and bus stops
- Protect IT infrastructure in basements and other areas susceptible to flooding

COLOR

White

PRODUCT FEATURES

TAA Compliant
Industrial Grade

TAA COMPLIANCE

Yes

PACKAGE CONTENTS

(4) Screw caps
(8) Screws
Quick Start Guide
N206-SB01-IND
Waterproof Electrical
Junction Box
(2) M16 cable glands

PRODUCT HIGHLIGHTS

IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.*
Designed for industrial cables and couplers—no guessing about compatibility
Standard IP68 rating guarantees water resistance at depths up to

	1.5 meters for up to 30 minutes. Surface-mount junction box includes wall-mounting hardware for immediate installation Lifetime limited warranty (Worldwide) Built to protect Gigabit Ethernet and digital signage applications in harsh environments Complies with Federal Trade Agreements Act standards for GSA Schedule purchases
TECHNOLOGY	Cat6 Cat5/5e
MATERIAL	high-impact polycarbonate
MOUNTING DETAILS	SCREW (X8), SCREW CAP (X4)
NUMBER OF PORTS	0
PROTECTION RATING	IP68
REGION	Global

□□□□:
□□□□:
□□□:
□□: