




Eaton N220-01K-BL

Cat6 Gigabit Bulk UTP Stranded 24 AWG
CMR PVC Cable, Blue, 1000 ft. (304.8 m) TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series bulk cable
CATALOG NUMBER	N220-01K-BL
UPC	037332196552
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	11.2 in
PRODUCT WIDTH	13.4 in
PRODUCT WEIGHT	21 lb
WARRANTY	Limited lifetime
COMPLIANCES	IEEE Certified RoHS REACH

□□□□	
CABLE JACKET RATING	CMR
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	N220-01K-BL Cat6 Gigabit Bulk Stranded 24 AWG CMR PVC Cable, Blue, 1000 ft.
SYSTEM REQUIREMENTS	Cat6
IEEE STANDARDS SUPPORTED	802.3ab
CONNECTOR TYPE	Bare Wire Networking-copper
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Channel-tested to 250 MHz/1 Gbps communications High-quality 24 AWG 4-pair stranded copper wire CMR-rated PVC jacket Lifetime limited warranty (Worldwide) Less impedance and structural return loss than 100 MHz wire Meets IEEE 802.3ab and ANSI/EIA/TIA 568 standards
SIDEA CONNECTOR1	BARE WIRE
SIDEB CONNECTOR1	BARE WIRE
SIDEB CONNECTOR3	BARE WIRE
TECHNOLOGY	Cat6
OPERATING TEMPERATURE RANGE	-4° to 167°F (-20° to 75°C)
STORAGE HUMIDITY RANGE	32° to 140°F (0° to 60°C)
STORAGE TEMPERATURE	32° to 140°F (0° to 60°C)
CONDUCTOR GAUGE	24 AWG
CABLE LENGTH	1000 Foot
OUTER CABLE DIAMETER	5.6 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 167°F (-20° to 75°C)
BANDWIDTH PER TIA STANDARD	250 MHz
MAXIMUM BANDWIDTH AS TESTED	500 MHz
CABLE SHIELDING	UTP



CABLE LENGTH RANGE	50ft and up (15M and up)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	Bulk cable
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	Bare wire
CABLE TYPE	Bulk
CABLE STYLE	Bulk



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

