



Eaton N222-01K-BK

Cat6 Gigabit Solid Core UTP PVC Bulk
Ethernet Cable, Black, 1000 ft. (304.8 m), TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series bulk cable
CATALOG NUMBER	N222-01K-BK
UPC	037332196620
PRODUCT LENGTH/DEPTH	13.78 in
PRODUCT HEIGHT	13.78 in
PRODUCT WIDTH	14.17 in
PRODUCT WEIGHT	28 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS IEEE Certified TAA Compliant REACH

□□□□	
CABLE JACKET RATING	CMR
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	N222-01K-BK Cat6 Gigabit Bulk Solid-Core PVC Cable, Black, 1000 ft.
SYSTEM REQUIREMENTS	Cat6
IEEE STANDARDS SUPPORTED	802.3ab
CONNECTOR TYPE	Networking-copper Bare Wire
PRODUCT FEATURES	TAA Compliant
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Less impedance and structural return loss than 100 MHz wire High-quality 23 AWG 4-pair solid copper wire Meets IEEE 802.3ab and ANSI/EIA/TIA 568 standards Rated for 550 MHz/1 Gbps communications CMR-rated PVC jacket
SIDEA CONNECTOR1	BARE WIRE
SIDEB CONNECTOR1	BARE WIRE
SIDEB CONNECTOR3	BARE WIRE
TECHNOLOGY	Cat6
OPERATING TEMPERATURE RANGE	-4° to 167°F (-20° to 75°C)
STORAGE HUMIDITY RANGE	32° to 140°F (0° to 60°C)
STORAGE TEMPERATURE	32° to 140°F (0° to 60°C)
CONDUCTOR GAUGE	23 AWG
CABLE LENGTH	1000 Foot
OUTER CABLE DIAMETER	6.2 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 167°F (-20° to 75°C)
BANDWIDTH PER TIA STANDARD	250 MHz
MAXIMUM BANDWIDTH AS TESTED	500 MHz
CABLE SHIELDING	UTP

□□

CABLE LENGTH RANGE	50ft and up (15M and up)
TAA COMPLIANCE	Yes
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	Bulk cable
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	Bare wire
CABLE TYPE	Bulk
CABLE STYLE	Solid Bulk



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

