



Eaton N223-01K-BK

Bulk Cat6a Cable – 10G, Solid Core UTP
CMR-rated Ethernet Cable, Black, 1000 ft.
(304.8 m)-N223-01K-BK


□□□□

PRODUCT NAME	Eaton Tripp Lite series bulk cable
CATALOG NUMBER	N223-01K-BK
UPC	037332278388
PRODUCT LENGTH/DEPTH	15.75 in
PRODUCT HEIGHT	9.45 in
PRODUCT WIDTH	15.75 in
PRODUCT WEIGHT	26.46 lb
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed



Powering Business Worldwide

□□□□	
CABLE JACKET RATING	CMR
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	N223-01K-BK Cat6a 10G Solid Core UTP Bulk Ethernet Cable, Black, 1000 ft. (305 m)
SYSTEM REQUIREMENTS	Cat6a
IEEE STANDARDS SUPPORTED	802.3af 802.3at
CONNECTOR TYPE	Bare Wire Networking-copper
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	23 AWG 4-pair solid copper cable rated for 10 Gbps Ethernet speeds Meets IEEE 802.3, TIA 568.2-D and ISO/IEC 11801 industry standards Lifetime limited warranty (Worldwide) 1000 ft. roll of cable comes in black for custom color-coded applications Recommended for premise installations in air ducts and drop ceilings
SIDEA CONNECTOR1	BARE WIRE
SIDEB CONNECTOR1	BARE WIRE
SIDEB CONNECTOR3	BARE WIRE
TECHNOLOGY	Cat6a
FEATURES	Flex Center
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	-20 TO 60 F (-4 TO 140 C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
CONDUCTOR GAUGE	23 AWG
CABLE LENGTH	1000 Foot
OUTER CABLE DIAMETER	6.3 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	50ft and up (15M and up)
CABLE SHEATH MATERIAL	UTP



CONNECTOR GROUP	Bulk cable
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	Bare wire
