



Eaton N223-01K-BL

Cat6a 10G-Certified Solid Core UTP CMR PVC Bulk Ethernet Cable, Blue, 1000 ft. (304.8 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series bulk cable
CATALOG NUMBER	N223-01K-BL
UPC	037332181787
PRODUCT LENGTH/DEPTH	15.75 in
PRODUCT HEIGHT	9.45 in
PRODUCT WIDTH	15.75 in
PRODUCT WEIGHT	26.46 lb
COMPLIANCES	RoHS IEEE Certified REACH

CABLE JACKET RATING	CMR
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	N223-01K-BL Cat6a 10G Bulk Solid-Core 4-Pair Unshielded PVC / CMR Cable, Blue, 1000 ft.
SYSTEM REQUIREMENTS	Cat6a
IEEE STANDARDS SUPPORTED	802.3ab
CONNECTOR TYPE	Bare Wire Networking-copper
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	Flame-retardant unshielded CMR-rated PVC jacket Meets IEEE 802.3, TIA 568-C.2 and ISO/IEC 11801 standards High-quality 23 AWG 4-pair solid copper wire, UnShielded Lifetime limited warranty (Worldwide) Rated for 10 Gbps communications Compliant with RoHS
SIDEA CONNECTOR1	BARE WIRE
SIDEB CONNECTOR1	BARE WIRE
SIDEB CONNECTOR3	BARE WIRE
TECHNOLOGY	Cat6a
OPERATING TEMPERATURE RANGE	-4° to 167°F (-20° to 75°C)
STORAGE HUMIDITY RANGE	32° to 140°F (0° to 60°C)
STORAGE TEMPERATURE	32° to 140°F (0° to 60°C)
CONDUCTOR GAUGE	23 AWG
CABLE LENGTH	1000 Foot
OUTER CABLE DIAMETER	7.6 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 167°F (-20° to 75°C)
BANDWIDTH PER TIA STANDARD	500 MHz
MAXIMUM BANDWIDTH AS TESTED	600 MHz
CABLE SHIELDING	UTP

CABLE LENGTH RANGE	50ft and up (15M and up)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	Bulk cable
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	Bare wire
CABLE TYPE	Bulk
CABLE STYLE	Bulk Solid



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

