



Eaton N235-001-6A

Cat6a Straight-Through Modular In-Line
Snap-In Coupler, (RJ45 F/F), TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series USB coupler
CATALOG NUMBER	N235-001-6A
UPC	037332189936
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.02 lb
COMPLIANCES	TAA Compliant

□□□□	
TYPE	RJ45 Coupler
COLOR	White
PACKAGE CONTENTS	N235-001-6A Cat6a Straight-Through Modular In-Line Snap-In Coupler (RJ45 F/F)
CONNECTOR COLOR	White
SYSTEM REQUIREMENTS	Cat6a
PRODUCT FEATURES	TAA Compliant
PRODUCT HIGHLIGHTS	Keystone design for use with standard data wallplate Heavy-duty polycarbonate housing 50-μ inch gold-plated contacts on RJ45 jacks Backward compatible with Cat6, Cat5e and Cat5 LANs Compatible with all Cat6a cables
SIDEA CONNECTOR1	RJ45 (FEMALE)
SIDEB CONNECTOR1	RJ45 (FEMALE)
SIDEB CONNECTOR3	RJ45 (FEMALE)
TECHNOLOGY	Cat6a
FEATURES	Flex Center
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
RELATIVE HUMIDITY	10% to 90% RH, Non- Condensing
STORAGE HUMIDITY RANGE	-40° to 154°F (-40° to 68°C)
STORAGE TEMPERATURE	-40° to 154°F (-40° to 68°C)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
POE TYPE	Type 4 High-Power (100W, IEEE 802.3bt)

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

