



Eaton N237-F18N-WHSH

Cat6 Keystone Jack Cable Assembly -
Unshielded, PoE+, RJ45 M/F, 18-in. (45.72
cm), Blue

□□□□

PRODUCT NAME	Eaton Tripp Lite series copper coupler
CATALOG NUMBER	N237-F18N-WHSH
UPC	037332250551
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.082 lb
COMPLIANCES	TAA Compliant

ACCESSORY CLASS	Networking accessories
COLOR	Blue
CABLE JACKET RATING	CMR CMR-LP LP5
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	N237-F18N-WHSH Cat6 Keystone Jack Cable Assembly, RJ45 M/F, 18 in., Blue
SYSTEM REQUIREMENTS	Cat6 PoE PoE device such as a security camera, Wireless Access Point (WAP) or other device requiring a network connection.
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	TAA Compliant
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Cat6 UTP patch cord rated for high-speed 550 MHz/1 Gbps communications Certified IEEE 802.3bt PoE++ cable saves you expense and effort of powering PoE devices individually Supports Type 4 Power over Ethernet (PoE) and PoE++ up to 100 watts Carries CMR-LP5 certification for withstanding temperatures up to 167°F (75°C) Ideal for security cameras, WAPs, LEDs and other ceiling-mount PoE++ devices 3-year limited warranty (Worldwide)
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (FEMALE)
ACCESSORY TYPE	Cable assembly kit
SIDEB CONNECTOR3	RJ45 (FEMALE)
TECHNOLOGY	PoE Cat6
FEATURES	Flex Center

OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
RELATIVE HUMIDITY	0-90% non-condensing
STORAGE HUMIDITY RANGE	-4° to 158°F (-20° to 70°C)
STORAGE TEMPERATURE	-4° to 158°F (-20° to 70°C)
POWER OVER ETHERNET (POE) POWER - MAX	24 W
CABLE LENGTH	1.5 Foot
OUTER CABLE DIAMETER	6.5 +/- 0.3 mm
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
TAA COMPLIANCE	Yes
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONNECTOR	RJ45 (female) RJ45 (male)
POE TYPE	Type 4 High-Power (100W, IEEE 802.3bt)
POWER OVER ETHERNET (POE)	100W (802.3bt)
CABLE STYLE	Regular
