



Eaton N250-012-6A-OF

12-Port Cat6a Wall-Mount Patch Panel -
PoE+ Compliant, 110, 568A/B, RJ45 Ethernet,
Offset Ports, TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series patch panel
CATALOG NUMBER	N250-012-6A-OF
UPC	037332285157
PRODUCT LENGTH/DEPTH	2.75 in
PRODUCT HEIGHT	9.96 in
PRODUCT WIDTH	2.55 in
PRODUCT WEIGHT	1.21 lb
COMPLIANCES	TAA Compliant RoHS REACH
CERTIFICATIONS	UL Listed

TYPE	Wall Mount
OPERATING HUMIDITY RANGE	10% TO 90% RH, NON-CONDENSING
STORAGE HUMIDITY RANGE	10% TO 90% RH, NON-CONDENSING
COLOR	Black
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	TAA Compliant Mounting Holes or Slots Numbered Ports Mounting Accessory Included
PACKAGE CONTENTS	Cable ties Installation instructions Mounting hardware N250-012-6A-OF 12-Port Wall-Mount Cat6a Patch Panel
PRODUCT HIGHLIGHTS	Panel easily snaps out of the frame for new connections, then snaps back into place Supports EIA/TIA 568A/B wiring standards for 110-type terminations 12 offset RJ45 and 110 ports numbered/labeled for immediate cable identification Lifetime limited warranty (Worldwide) PoE+ patch panel prevents spark-gap erosion that can affect transmission Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
SIDEA CONNECTOR1	110 IDC
SIDEB CONNECTOR1	RJ45 (FEMALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-40° to 154°F (-40° to 68°C)
SIDEB CONNECTOR3	RJ45 (FEMALE)
TECHNOLOGY	Cat6a
NUMBER OF PORTS	12
TOTAL NUMBER OF PORTS	12

HOUSING	SECC
CONNECTOR GROUP	111 block RJ45
MOUNTING DETAILS	WALL MOUNT
TAA COMPLIANCE	Yes
PANEL STYLE	Punchdown
CONNECTOR	RJ45 (female) 110 IDC
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
TERMINATION TYPE	110-type
