



Eaton N261-100-BK

Cat6a 10G Snagless Molded UTP Ethernet Cable (RJ45 M/M), PoE, Black, 100 ft. (30.5 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N261-100-BK
UPC	037332277589
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	17 in
PRODUCT WIDTH	14 in
PRODUCT WEIGHT	2.51 lb
WARRANTY	Limited lifetime
COMPLIANCES	IEEE Certified REACH RoHS
CERTIFICATIONS	cUL Listed UL Listed

SPECIAL FEATURES	5% to 85% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	N261-100-BK Cat6a 10G Snagless Molded UTP Ethernet Cable (RJ45 M/M), PoE, Black, 100 ft. (30.5 m)
SYSTEM REQUIREMENTS	Cat6a PoE
CONNECTOR PLATING	Nickel
IEEE STANDARDS SUPPORTED	802.3at 802.3ab 802.3af 802.3an
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector PoE Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	Black jacket permits fast, easy identification in a crowded switch or patch panel Snagless RJ45 connectors prevent tabs from being damaged during installation Allows installation of PoE devices in hard-to-reach areas or away from AC outlets Supports PoE to save you expense and effort of powering PoE devices individually Cat6a UTP Ethernet cable rated for high-speed 10 Gbps communications Lifetime limited warranty (Worldwide)
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6a
FEATURES	Flex Center
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING	-4° to 140°F (-20° to 60°C)

