



Eaton N262-001-BL

Cat6a 10G Certified Snagless Shielded STP Ethernet Cable (RJ45 M/M), PoE, Blue, 1 ft. (0.31 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N262-001-BL
UPC	037332188267
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.05 lb
COMPLIANCES	IEEE Certified RoHS REACH
CERTIFICATIONS	cUL Listed UL Listed

SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	1-ft. (0.31 m) Cat6a Blue Patch Cable
SYSTEM REQUIREMENTS	Cat6a
CONNECTOR PLATING	Nickel
IEEE STANDARDS SUPPORTED	802.3at
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	Each cable Fluke® Tested and Verified 10Gbps Over Copper Lifetime limited warranty (Worldwide) 1-ft. (0.31 m) Augmented Cat6 (CAT6a) Shielded (STP) Snagless Patch Cable, Blue
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6a
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 140°F (-15° to 60°C)
CONDUCTOR GAUGE	26 AWG
CABLE LENGTH	1 Foot
OUTER CABLE DIAMETER	6.2 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
BANDWIDTH PER TIA STANDARD	500 MHz
MAXIMUM BANDWIDTH AS TESTED	600 MHz

CABLE SHIELDING	STP
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE SHEATH MATERIAL	STP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
POWER OVER ETHERNET (POE)	15.4W (802.3af)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Snagless
CABLE STYLE	Snagless
