



Eaton N280-005-BK

SFP+ 10Gbase-CU Passive Twinax Copper Cable, SFP-H10GB-CU1-5M Compatible, Black, 5 ft. (1.52 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series direct attach cable
CATALOG NUMBER	N280-005-BK
UPC	037332178138
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12 in
PRODUCT WIDTH	10.5 in
PRODUCT WEIGHT	0.23 lb
COMPLIANCES	RoHS

SPECIAL FEATURES	5% to 85% RH
-------------------------	--------------

COLOR	Black
--------------	-------

CABLE JACKET COLOR	Black
---------------------------	-------

PACKAGE CONTENTS	1.5 m. (5 ft.) 30Awg SFP+ High Speed Passive Copper 10Gbps Cable
-------------------------	--

SYSTEM REQUIREMENTS

SFP+ Direct Attach Cable (DAC) Twinaxial cables conform to SFF-8431 standards, and as such can be used with the following manufacturers equipment that are open to 3rd party cables:
QLOGIC * EMULEX * JUNIPER * ARISTA * IBM * DELL * EXTREME EMC * BROADCOM * FINISAR * VOLTAIRE * CISCO
CONFIRMED EQUIPMENT LIST (*ensure the latest firmware and software is installed) CISCO NEXUS * CISCO CATALYST * CISCO CATALYST 3750x CISCO CATALYST 2960 CISCO CATALYST 3500 CISCO CATALYST 3550 CISCO NEXUS 5010 ARISTA 70505-64 QUANTA T3048 EXTREME X250E JUNIPER EX3200 NOT COMPATIBLE TO 3RD PARTY CABLES: HP and BROCADE
SFP+ Direct Attach Cable (DAC) Twinaxial cables conform to SFF-8431 standards, and as such can be used with the following manufacturers equipment that are open to 3rd party cables:
QLOGIC * EMULEX * JUNIPER * ARISTA * IBM * DELL * EXTREME EMC * BROADCOM * FINISAR * VOLTAIRE * CISCO
CONFIRMED EQUIPMENT LIST (*ensure the latest firmware and software is installed) CISCO NEXUS * CISCO CATALYST * CISCO CATALYST 3750x CISCO CATALYST 2960 CISCO CATALYST 3500 CISCO CATALYST 3550 CISCO

NEXUS 5010 ARISTA
 70505-64 QUANTA T3048
 EXTREME X250E JUNIPER
 EX3200 NOT COMPATIBLE
 TO 3RD PARTY CABLES: HP
 and BROCADE
 SFP+ Direct Attach Cable (DAC)
 Twinaxial cables conform to SFF-8431 standards, and as such can be used with the following manufacturers equipment that are open to 3rd party cables:
 QLOGIC * EMULEX * JUNIPER * ARISTA * IBM * DELL * EXTREME EMC * BROADCOM * FINISAR * VOLTAIRE * CISCO
 CONFIRMED EQUIPMENT LIST (*ensure the latest firmware and software is installed)

IEEE STANDARDS SUPPORTED	802.3BA
CONNECTOR TYPE	Networking-copper
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	Equivalent to Cisco SFP-H10GB-CU1-5M Fully compliant to MSA SFF-8431 specification Lifetime limited warranty (Worldwide) 1.5 m. (5 ft.) 30AWG SFP+ High Speed Passive Copper 10Gbps Cable Low Cost alternative to Fiber Optic
SIDEA CONNECTOR1	SFP+ (MALE)
SIDEB CONNECTOR1	SFP+ (MALE)
SIDEB CONNECTOR3	SFP+ (MALE)
OPERATING HUMIDITY	5% to 85% RH
OPERATING TEMPERATURE RANGE	32° to 158°F (0° to 70°C)
STORAGE HUMIDITY RANGE	5% to 85% RH
STORAGE TEMPERATURE	-4° to 185°F (-20° to 85°C)
BEND RADIUS - MIN	23mm
AWG-SIZE	30
CABLE LENGTH	5 Foot
OUTER CABLE DIAMETER	4.2mm
OPERATING	32° to 158°F (0° to 70°C)

TEMPERATURE	
COMPATIBLE BRAND	Arista
	Voltaire
	Cisco
	EMC
	Extreme
	Broadcom
	Emulex
	QLogic
	Juniper
	Dell
	Finisar
	IBM
CONNECTOR GROUP	SFP+
CONNECTOR	SFP+ (male)
CABLE TYPE	Passive

□□□□:
□□□□:
□□□:
□□: