



Eaton N282-03M-BK

QSFP+ to QSFP+ 40Gb Passive DAC Copper
Infiniband Cable, QSFP-H40G-CU3M
Compatible, 3M (9.84 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series direct attach cable
CATALOG NUMBER	N282-03M-BK
UPC	037332181565
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	17 in
PRODUCT WIDTH	14 in
PRODUCT WEIGHT	0.55 lb
COMPLIANCES	RoHS MSA SFF-8436

□□□□	
SPECIAL FEATURES	5% to 85% RH
COLOR	Black
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	3 Meter, QSFP+ to QSFP+ High Speed Passive Copper 40GB Cable
SYSTEM REQUIREMENTS	Networking Switch or other hardware with open QSFP+ Port(s)
IEEE STANDARDS SUPPORTED	802.3BA
CONNECTOR TYPE	Networking-copper
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	40 Gbps
PRODUCT HIGHLIGHTS	SDR, DDR, and QDR Compatible Lifetime limited warranty (Worldwide) Meets or Exceeds 40-Gigabit Ethernet 40GBASE-CR4 standards Fully compliant to the latest QSFP+ MSA (Multi Source Agreement) Compatible with Cisco QSFP-H40G-CU3M 40Gbps QSFP+ to QSFP+ 3 Meter patch cable
SIDEA CONNECTOR1	QSFP+ (MALE)
SIDEB CONNECTOR1	QSFP+ (MALE)
SIDEB CONNECTOR3	QSFP+ (MALE)
OPERATING HUMIDITY	5% to 85% RH
OPERATING TEMPERATURE RANGE	32° to 158°F (0° to 70°C)
STORAGE HUMIDITY RANGE	5% to 85% RH
STORAGE TEMPERATURE	-4° to 185°F (-20° to 85°C)
BEND RADIUS - MIN	38mm
AWG-SIZE	30
CABLE LENGTH	9.8 Foot
OUTER CABLE DIAMETER	6.5mm
OPERATING TEMPERATURE	32° to 158°F (0° to 70°C)
COMPATIBLE BRAND	Cisco
CONNECTOR GROUP	QSFP+
CONNECTOR	QSFP+ (male)
CABLE TYPE	Passive



