



Eaton N286-01GSX-MDLC

Cisco-Compatible GLC-SX-MMD 1000Base-SX
SFP Transceiver, DDM, Multimode LC,
850nm, 550M

□□□□

PRODUCT NAME	Eaton Tripp Lite series multimode fiber transceiver
CATALOG NUMBER	N286-01GSX-MDLC
UPC	037332185488
PRODUCT LENGTH/DEPTH	4.84 in
PRODUCT HEIGHT	0.87 in
PRODUCT WIDTH	2.87 in
PRODUCT WEIGHT	0.1 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS



Powering Business Worldwide

□□□□	
PRODUCT FEATURES	Multi-Source Agreement (MSA) Compliant
PACKAGE CONTENTS	N286-01GSX-MDLC Transceiver Quick Start Guide
PRODUCT HIGHLIGHTS	500 meter transmission distance using 50/125 MMF cabling Compliant with SFP Multi-Source Agreement (MSA) standards 300 meter transmission distance using 62.5/125 MMF cabling 3-year limited warranty (Worldwide) Cisco switch compatible...Comparable to GLC-SX-MMD=
SIDEA CONNECTOR1	SFP (MALE)
SIDEB CONNECTOR1	LC DUPLEX (FEMALE)
NETWORK COMPATIBILITY	1 Gbps (Gigabit)
BRAND COMPATIBILITY	Cisco
OPTICAL PORT	LC
TRANSMISSION DISTANCE	
OPERATING TEMPERATURE	• 32 to 158 F (0 to 70 C) • 32° to 158°F (0° to 70°C)
STORAGE TEMPERATURE RANGE	-40° to 185°F (-40° to 85°C)
DATA TRANSFER RATE	1 Gbps
WAVELENGTH	850 nm
CONNECTOR	SFP (MALE) LC duplex (female)

