



## Eaton N286-10GLR-SLC

Cisco-Compatible SFP-10G-LR SFP  
Transceiver, 10GBase-LR, DDM, Singlemode  
LC , 1310 nm, 10 km

□□□□

<b>PRODUCT NAME</b>	Eaton Tripp Lite series singlemode fiber transceiver
<b>CATALOG NUMBER</b>	N286-10GLR-SLC
<b>UPC</b>	037332197429
<b>PRODUCT LENGTH/DEPTH</b>	2.24 in
<b>PRODUCT HEIGHT</b>	0.331 in
<b>PRODUCT WIDTH</b>	0.52 in
<b>PRODUCT WEIGHT</b>	0.05 lb
<b>COMPLIANCES</b>	RoHS

PRODUCT FEATURES	Multi-Source Agreement (MSA) Compliant
PRODUCT HIGHLIGHTS	Supports data transfer rates up to 10 Gbps 100% compatible with Cisco networking hardware Complies with MSA standards Supports digital diagnostics monitoring (DDM) Transmits up to 6 mi. (10 km) with 9/125 SMF cabling
SIDEA CONNECTOR1	SFP+ (MALE)
SIDEB CONNECTOR1	LC DUPLEX (FEMALE)
NETWORK COMPATIBILITY	10 Gbps
BRAND COMPATIBILITY	Cisco
OPTICAL PORT	LC
TRANSMISSION DISTANCE	10 km
OPERATING TEMPERATURE	<ul style="list-style-type: none"><li>• 32 to 158 F (0 to 70 C)</li><li>• 32° to 158°F (0° to 70°C)</li></ul>
STORAGE TEMPERATURE RANGE	-40° to 185°F (-40° to 85°C)
DATA TRANSFER RATE	10 Gbps
WAVELENGTH	1310 nm

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: