



Eaton N286-10GSR-MDLC

Cisco-Compatible SFP-10G-SR 10Gbase-SR SFP+ Transceiver, DDM, Multimode LC, 850nm, 300M

□□□□

PRODUCT NAME	Eaton Tripp Lite series multimode fiber transceiver
CATALOG NUMBER	N286-10GSR-MDLC
UPC	037332185495
PRODUCT LENGTH/DEPTH	2.24 in
PRODUCT HEIGHT	0.331 in
PRODUCT WIDTH	0.52 in
PRODUCT WEIGHT	0.05 lb
COMPLIANCES	RoHS

PRODUCT FEATURES	Multi-Source Agreement (MSA) Compliant
PACKAGE CONTENTS	N286-10GSR-MDLC Quick Start Guide
PRODUCT HIGHLIGHTS	3-year limited warranty (Worldwide) Cisco switch compatible...Comparable to SFP-10G-SR= Compliant with SFP Multi-Source Agreement (MSA) standards 300 meter transmission distance using 10Gb 50/125 MMF cabling
SIDE A CONNECTOR1	SFP+ (MALE)
SIDE B CONNECTOR1	LC DUPLEX (FEMALE)
NETWORK COMPATIBILITY	10 Gbps
BRAND COMPATIBILITY	Cisco
OPTICAL PORT	LC
TRANSMISSION DISTANCE	
OPERATING TEMPERATURE	• 32 to 158 F (0 to 70 C) • 32° to 158°F (0° to 70°C)
STORAGE TEMPERATURE RANGE	-40° to 185°F (-40° to 85°C)
DATA TRANSFER RATE	10 Gbps
WAVELENGTH	850 nm
CONNECTOR	SFP+ (male) LC duplex (female)

<