



Eaton N306-30M

Duplex Multimode 62.5/125 Fiber Patch Cable (SC/SC), 30M (100 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N306-30M
UPC	037332135315
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12 in
PRODUCT WIDTH	10.5 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	REACH RoHS

□□□□	
CABLE JACKET RATING	OFNR
CABLE JACKET COLOR	Orange
PACKAGE CONTENTS	30 Meter (100ft) duplex MMF cable SC/SC 62.5/125 fiber
CONNECTOR COLOR	White
SYSTEM REQUIREMENTS	Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/SC connectors
CONNECTOR TYPE	Networking-fiber
CABLE JACKET MATERIAL	LSZH
NETWORK SPEED	10 Gbps 1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Attenuation loss meets or exceeds the latest industry standards Premium PVC 62.5/125μ m multimode patch cables
SIDEA CONNECTOR1	SC DUPLEX (MALE)
SIDEB CONNECTOR1	SC DUPLEX (MALE)
TECHNOLOGY	Multimode
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	35% to 65% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
BEND RADIUS - MIN	20 mm (Dynamic); 10 mm (Static)
CLAD DIAMETER	125
CORE DIAMETER - MAX	62.5
INSERTION LOSS	≤ 0.20 dB
NUMBER OF FIBERS	2
FIBER CABLE LENGTH	30M (98.4 ft)
CONNECTOR GROUP	SC
CONNECTOR	SC duplex (male)
ATTENUATION 850NM	3.0 dB/km
ENDFACE POLISH	PC
OPTICAL MODE	OM1
FIBER TYPE	62.5/125



