



Eaton N320-405

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC), 123M (405 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N320-405
UPC	037332140463
PRODUCT LENGTH/DEPTH	10.3 in
PRODUCT HEIGHT	10.1 in
PRODUCT WIDTH	4.7 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	REACH RoHS

CABLE JACKET RATING	OFNR
CABLE JACKET COLOR	Orange
PACKAGE CONTENTS	405-ft. (123.44 m) LC/LC Duplex MMF 62.5/125 Fiber Patch Cable
CONNECTOR COLOR	Gray
SYSTEM REQUIREMENTS	Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors
CONNECTOR TYPE	Networking-fiber
CABLE JACKET MATERIAL	LSZH
NETWORK SPEED	1 Gbps (Gigabit) 10 Gbps
PRODUCT HIGHLIGHTS	Insertion loss testing performed on every connector (0.2dB typical) Lifetime limited warranty (Worldwide) Manufactured from 62.5/125 duplex (Zipcord) fiber
SIDEA CONNECTOR1	LC DUPLEX (MALE)
SIDEB CONNECTOR1	LC DUPLEX (MALE)
TECHNOLOGY	Multimode
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	35% to 65% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
BEND RADIUS - MIN	20 mm (Dynamic); 10 mm (Static)
CLAD DIAMETER	125
CORE DIAMETER - MAX	62.5
INSERTION LOSS	≤ 0.20 dB
NUMBER OF FIBERS	2
FIBER CABLE LENGTH	123.5M (405 ft)
CONNECTOR GROUP	LC
CONNECTOR	LC duplex (male)
ATTENUATION 850NM	3.0 dB/km
ENDFACE POLISH	PC
OPTICAL MODE	OM1
FIBER TYPE	62.5/125

