



Eaton N356-10M

Duplex Singlemode 9/125 Fiber Patch Cable
(SC/SC), 10M (33 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N356-10M
UPC	037332120342
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.19 lb
COMPLIANCES	REACH RoHS

□□□□	
CABLE JACKET RATING	OFNR
CABLE JACKET COLOR	Yellow
PACKAGE CONTENTS	10-meter (33ft) Duplex Singlemode Fiber Patch Cable, SC/SC
CONNECTOR COLOR	Blue
CONNECTOR TYPE	Networking-fiber
CABLE JACKET MATERIAL	LSZH
NETWORK SPEED	1 Gbps (Gigabit) 40 Gbps 10 Gbps 100 Gbps
PRODUCT HIGHLIGHTS	Attenuation loss meets or exceeds the latest industry standards Premium PVC 9/125 micron singlemode patch cables Lifetime limited warranty (Worldwide) Twice the bandwidth throughput of multimode cable
SIDEA CONNECTOR1	SC DUPLEX (MALE)
SIDEB CONNECTOR1	SC DUPLEX (MALE)
TECHNOLOGY	Singlemode
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	35% to 65% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
BEND RADIUS - MIN	20 mm (Dynamic); 10 mm (Static)
CLAD DIAMETER	125
CORE DIAMETER - MAX	9
INSERTION LOSS	≤ 0.30 dB
NUMBER OF FIBERS	2
FIBER CABLE LENGTH	10M (32.8 ft)
CONNECTOR GROUP	SC
CONNECTOR	SC duplex (male)
ATTENUATION 1310NM	0.36 dB/km
ATTENUATION 1550NM	0.22 dB/km
ENDFACE POLISH	UPC
OPTICAL MODE	OS2


