



Eaton N356-30M

Duplex Singlemode 9/125 Fiber Patch Cable
(SC/SC), 30M (100 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N356-30M
UPC	037332134837
PRODUCT LENGTH/DEPTH	2.5 in
PRODUCT HEIGHT	12 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	0.74 lb
COMPLIANCES	REACH RoHS

CABLE JACKET RATING	OFNR
CABLE JACKET COLOR	Yellow
PACKAGE CONTENTS	30-meter (100ft) Duplex Singlemode Fiber Patch Cable, SC/SC
CONNECTOR COLOR	Blue
SYSTEM REQUIREMENTS	Any fiber optic hardware or NIC card requiring singlemode duplex cable with SC/SC connectors
CONNECTOR TYPE	Networking-fiber
CABLE JACKET MATERIAL	LSZH
NETWORK SPEED	100 Gbps 1 Gbps (Gigabit) 10 Gbps 40 Gbps
PRODUCT HIGHLIGHTS	Premium PVC 9/125 micron singlemode patch cables Lifetime limited warranty (Worldwide) Twice the bandwidth throughput of multimode cable Attenuation loss meets or exceeds the latest industry standards
SIDEA CONNECTOR1	SC DUPLEX (MALE)
SIDEB CONNECTOR1	SC DUPLEX (MALE)
TECHNOLOGY	Singlemode
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	35% to 65% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
BEND RADIUS - MIN	20 mm (Dynamic); 10 mm (Static)
CLAD DIAMETER	125
CORE DIAMETER - MAX	9
INSERTION LOSS	≤ 0.30 dB
NUMBER OF FIBERS	2
FIBER CABLE LENGTH	30M (98.4 ft)
CONNECTOR GROUP	SC
CONNECTOR	SC duplex (male)
ATTENUATION 1310NM	0.36 dB/km

ATTENUATION 1550NM	0.22 dB/km
ENDFACE POLISH	UPC
OPTICAL MODE	OS2
FIBER TYPE	9/125
