



Eaton N482-04U

Enclosure for 28 High-Density Fiber
Cassettes, 4U

□□□□

PRODUCT NAME	Eaton Tripp Lite series cassette
CATALOG NUMBER	N482-04U
UPC	037332262813
PRODUCT LENGTH/DEPTH	16.93 in
PRODUCT HEIGHT	6.97 in
PRODUCT WIDTH	18.98 in
PRODUCT WEIGHT	14.33 lb
COMPLIANCES	REACH RoHS

COLOR	Silver Black
PACKAGE CONTENTS	N482-04U High-Density Modular Fiber Cassette Enclosure Quick Start Guide
SYSTEM REQUIREMENTS	Compatible with N482- Series fiber cassettes
PRODUCT FEATURES	Rackmountable
PRODUCT HIGHLIGHTS	Heavy-duty steel enclosure accommodates up to 28 N482-Series fiber cassettes Patches as many as 336 duplex LC ports (672 fiber connections) in 4U of rack space Easy-access fold-down front door panel protects connections and can be removed Helps you interconnect any combo of 10 Gb, 40 Gb and 100/120 Gb network equipment Optional rear-mount cable management bracket allows proper routing of cabling
RACK HEIGHT	4U
TECHNOLOGY	Singlemode Multimode
OPERATING HUMIDITY	5% to 85% RH, Non- Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	5% to 85% RH, Non- Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
PRIMARY FORM FACTOR	Rackmount
MATERIAL OF CONSTRUCTION	Chassis and Wire Manager: Steel; Blank Plate: Plastic
CASSETTE CAPACITY	28
MAXIMUM DEVICE DEPTH	16.9 in
PANEL STYLE	Cassette Type
CASSETTE TYPE	Panel Enclosure
CABLE MANAGEMENT	Bracket

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

