



## Eaton N482-2M12-LC12

40Gb to 10Gb Breakout Cassette - (x2) 12-Fiber OM4 MTP/MPO ( Male with Pins ) to (x12) LC

□□□□

<b>PRODUCT NAME</b>	Eaton Tripp Lite series cassette
<b>CATALOG NUMBER</b>	N482-2M12-LC12
<b>UPC</b>	037332184542
<b>PRODUCT LENGTH/DEPTH</b>	4.7 in
<b>PRODUCT HEIGHT</b>	1.2 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.55 lb
<b>COMPLIANCES</b>	RoHS

**COLOR**

Black

**PACKAGE CONTENTS**

Quick Start Guide  
N482-2M12-LC12 40Gb to  
10Gb Breakout Cassette -  
(x2) 12-Fiber OM4  
MTP/MPO to (x12) LC

**SYSTEM REQUIREMENTS**

Cassette designed  
specifically for use with  
N820-, N821-, N844- and  
N845-Series cables  
12-Fiber MTP Ports are  
Polarity B, Optimized for  
Parallel Optics, Base-8  
Connectivity  
Guaranteed compatibility  
when used with  
recommended cabling

**PRODUCT HIGHLIGHTS**

Max insertion loss of  
0.35dB falls well under the  
IEEE 802.3ae maximum  
channel loss spec of <25dB

High Density Fiber  
Cassette for use with  
N482-01U and N482-02U  
High Density Fiber  
Enclosure Panels  
Complies with IEEE  
802.3ae (10GbE) and ANSI  
T11.2 (Fibre Channel)  
requirements

Internal OM4 wiring  
12-Fiber MTP ports are  
Polarity B, Optimized for  
Parallel Optics, Base-8  
Connectivity  
Factory terminated  
connectors reduce the  
time and labor required of  
field connector  
terminations  
40Gb to 10Gb Breakout  
Cassette, with (x12) LC  
connections to Normal 0  
false false false EN-US X-  
NONE X-NONE  
MicrosoftInternetExplorer4

Guaranteed compatibility  
when used with  
recommended cabling  
Cassette designed  
specifically for use with  
cables, such as the N820-  
N821-, N844- and N845-  
Series cables

SIDEA CONNECTOR1	12F MTP/MPO (MALE)
SIDEB CONNECTOR1	LC DUPLEX (FEMALE)
TECHNOLOGY	Multimode
FEATURES	Flex Center
NUMBER OF PORTS	12
