



Eaton N482-3M8-LC12

40/100Gb Breakout Cassette, 40Gb to 4 x 10Gb, 100Gb to 4 x 25Gb (x3) 8-Fiber OM4 MTP/MPO (Male with Pins) to (x12) LC Duplex, Type-B Polarity

□□□□

PRODUCT NAME	Eaton Tripp Lite series cassette
CATALOG NUMBER	N482-3M8-LC12
UPC	037332200327
PRODUCT LENGTH/DEPTH	1.18 in
PRODUCT HEIGHT	4.72 in
PRODUCT WIDTH	3.46 in
PRODUCT WEIGHT	0.3 lb
COMPLIANCES	RoHS

PACKAGE CONTENTS	N482-3M8-LC12 40 GB to 10 GB Breakout Cassette Quick Start Guide
SYSTEM REQUIREMENTS	8-fiber MTP ports are Polarity B, optimized for parallel optics and Base-8 Connectivity Guaranteed compatibility with recommended cabling, including N820-, N821-, N844-, N845- and N858-Series cables QSFP switches that use 8-fiber per port to support 4 x LC 10 GB breakout
PRODUCT HIGHLIGHTS	Simple installation with no tools required Base-8 Fiber compatible with both QSFP+ 40GBASE-SR4 to SFP+ 10GBASE-SR and QSFP28 100GBASE-SR4 to SFP28 25GBASE-SR connections Supports 40 GbE internally using OM4 fiber optic cable Designed for use with recommended cabling For use with N482-01U or N482-02U chassis Factory-terminated OM4 connectors
SIDEA CONNECTOR1	8F MTP/MPO (MALE)
SIDEB CONNECTOR1	LC DUPLEX (FEMALE)
TECHNOLOGY	Multimode
FEATURES	Flex Center
NUMBER OF PORTS	12

□□□□:
□□□□:
□□□:
□□: