



Eaton N484-3M8-LC12

40/100Gb Breakout Cassette, 40Gb to 4 x 10Gb, 100Gb to 4 x 25Gb, (x3) 8-Fiber MTP/MPO to (x12) LC Duplex, Type-B Polarity

□□□□

PRODUCT NAME	Eaton Tripp Lite series cassette
CATALOG NUMBER	N484-3M8-LC12
UPC	037332191366
PRODUCT LENGTH/DEPTH	3.7 in
PRODUCT HEIGHT	1.4 in
PRODUCT WIDTH	4.4 in
PRODUCT WEIGHT	0.8 lb
COMPLIANCES	RoHS



Powering Business Worldwide

PACKAGE CONTENTS

Quick Start Guide
40/100Gb Breakout
Cassette, 40Gb to 4 x
10Gb, 100Gb to 4 x
25Gb, (x3) 8-Fiber OM4
MTP/MPO to (x12) LC
Duplex

SYSTEM REQUIREMENTS

8-fiber MTP ports are
Polarity B, optimized for
parallel optics and Base-8
Connectivity
Guaranteed compatibility
with recommended
cabling, including N820-,
N821-, N844-, N845- and
N858 Series cables
QSFP switches that use 8-
fiber per port to support 4
x LC 10 GB breakout

PRODUCT HIGHLIGHTS

For use with N484-01U or
N484-00U chassis
Simple installation with no
tools required
Factory-terminated
connectors
Designed for use with
recommended cabling
Supports 40 GbE internally
using OM4 fiber optic
cable
Base-8 Fiber compatible
with both QSFP+
40GBASE-SR4 to SFP+
10GBASE-SR and QSFP28
100GBASE-SR4 to SFP28
25GBASE-SR connections

SIDE A CONNECTOR1	8F MTP/MPO (MALE)
--------------------------	-------------------

SIDE B CONNECTOR1	LC DUPLEX (FEMALE)
--------------------------	--------------------

TECHNOLOGY	Multimode
-------------------	-----------

FEATURES	Flex Center
-----------------	-------------

NUMBER OF PORTS	12
------------------------	----

