



Eaton N48LSS-32X32

Spine-Leaf MPO Panel with Key-Up to Key-Down MTP/MPO Adapter - 12F MTP/MPO-APC M/M, 8F OS2 Singlemode, 32 x 32 Ports, 1U

□□□□

PRODUCT NAME	Eaton Tripp Lite series preloaded fiber optic patch panel
CATALOG NUMBER	N48LSS-32X32
UPC	037332268792
PRODUCT LENGTH/DEPTH	18.97 in
PRODUCT HEIGHT	1.73 in
PRODUCT WIDTH	14.76 in
PRODUCT WEIGHT	6.172 lb
WARRANTY	Limited lifetime
COMPLIANCES	CE Marked RoHS REACH



Powering Business Worldwide

□□□□	
TYPE	Spine-Leaf
COLOR	Black
PACKAGE CONTENTS	Owner's manual N48LSS-32X32 Spine-Leaf MPO Panel, 32 x 32 Ports, 1U
CONNECTOR COLOR	Black
PRODUCT FEATURES	All-in-One Kit Labeled Ports Numbered Ports Built-in Cables
NETWORK SPEED	400 Gbps 100 Gbps 40 Gbps
PRODUCT HIGHLIGHTS	Replaces standard MTP/MPO-to-LC cross- connect to reduce troubleshooting and labor Mounts easily into 1U of space in your EIA-standard 19 in. rack or cabinet All-in-one solution for 9/125 singlemode OS2 8- fiber network cabling 1U patch panel designed for cost-effective spine and leaf cabling Lifetime limited warranty (Worldwide) Front and rear wire managers help organize cables and eliminate clutter
RACK HEIGHT	1U
SIDE A CONNECTOR1	12F MTP/MPO (MALE)
SIDE B CONNECTOR1	12F MTP/MPO (MALE)
TECHNOLOGY	Fiber
FEATURES	Flex Center
OPERATING HUMIDITY	5% to 85% RH, Non- Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	5% to 85% RH, Non- Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
CLAD DIAMETER	125
CORE DIAMETER - MAX	9
INSERTION LOSS	≤ 0.70 dB

□□

NUMBER OF FIBERS	8
PANEL DIMENSIONS	17.56" X 1.73" X 14.76"
PRIMARY FORM FACTOR	Rackmount
NUMBER OF PORTS	64
TOTAL NUMBER OF PORTS	64
PANEL STYLE	Spine-Leaf
WAVELENGTH	1310 nm 1550 nm
CONNECTOR	12F MTP/MPO (male)
ATTENUATION 1310NM	0.36 dB / km
ATTENUATION 1550NM	0.22 dB / km
ENDFACE POLISH	APC
OPTICAL MODE	OS2
MODE	Singlemode
OPTICAL PORT	MPO/MTP
NETWORK SPEED SUPPORT	100 Gbps 40 Gbps 400 Gbps
FIBER TYPE	9/125
