



Eaton N520-15M

Duplex Multimode 50/125 Fiber Patch Cable
(LC/LC), 15M (50 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N520-15M
UPC	037332119490
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	6.4 in
PRODUCT WEIGHT	0.2 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS

□□□□	
CABLE JACKET RATING	OFNR
CABLE JACKET COLOR	Orange
PACKAGE CONTENTS	15M duplex MMF cable LC/LC 50/125 fiber
CONNECTOR COLOR	Gray
SYSTEM REQUIREMENTS	Any fiber optic hardware or NIC card requiring multimode duplex cable with LC/LC connectors
CONNECTOR TYPE	Networking-fiber
CABLE JACKET MATERIAL	LSZH
NETWORK SPEED	10 Gbps 25 Gbps 1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Premium PVC multimode patch cables Attenuation loss meets or exceeds the latest industry standards Backward compatible with 62.5 micron fiber Built-in headroom for future applications Higher bandwidth optimized for gigabit and 10Gbps networks
SIDEA CONNECTOR1	LC DUPLEX (MALE)
SIDEB CONNECTOR1	LC DUPLEX (MALE)
TECHNOLOGY	Multimode
OPERATING HUMIDITY	5% to 85% RH, Non- Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	35% to 65% RH, Non- Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
BEND RADIUS - MIN	20 mm (Dynamic); 10 mm (Static)
CLAD DIAMETER	125
CORE DIAMETER - MAX	50
INSERTION LOSS	≤ 0.20 dB
NUMBER OF FIBERS	2
FIBER CABLE LENGTH	15M (49.2 ft)
CONNECTOR GROUP	LC
CONNECTOR	LC duplex (male)
ATTENUATION 850NM	3.0 dB/km

ENDFACE POLISH	PC
OPTICAL MODE	OM2
FIBER TYPE	50/125
