




Eaton N784-001-SC-15

10/100 SC Singlemode Fiber to Ethernet
Media Converter, 15km, 1310nm

□□□□

PRODUCT NAME	Eaton Tripp Lite series media converter
CATALOG NUMBER	N784-001-SC-15
UPC	037332184139
PRODUCT LENGTH/DEPTH	2.76 in
PRODUCT HEIGHT	3.7 in
PRODUCT WIDTH	1.02 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS CE Marked FCC Compliant

□□□□	
TYPE	Fiber to Ethernet
ACCESSORIES	External Power Supply (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V/2A)
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
COLOR	Black
PACKAGE CONTENTS	N784-001-SC-15 Media Converter External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz; Output: 5V, 1.2A) Owner's Manual
SYSTEM REQUIREMENTS	10/100 Ethernet Network Singlemode SC Fiber cable
CONNECTOR TYPE	Networking-fiber Networking-copper
PRODUCT FEATURES	Auto MDIX Support Wavelength Division Multiplexing (WDM)
NETWORK SPEED	10 Mbps 100 Mbps (Fast Ethernet) 10 Mbps; 100 Mbps
PRODUCT HIGHLIGHTS	2-year limited warranty (Worldwide) Supports Singlemode cable up to 15 KM Auto detects Full/Half Duplex Transfer Mode Extends a 100Mb Ethernet signal up to 15km over Singlemode Fiber Optic Cable
NETWORK SPEED DETAILS	10 Mbps; 100 Mbps
PACKAGING TYPE	Box
EXTERNAL POWER SUPPLY CERTIFICATIONS	FCC cUL WEEE CE
SIDEA CONNECTOR1	RJ45 (FEMALE)
SIDEB CONNECTOR1	SC DUPLEX (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.5 x 11 mm, positive pin, negative sleeve
TECHNOLOGY	Cat5/5e Singlemode
FEATURES	Flex Center
OPERATING	-4° to 140°F (-20° to 60°C)



TEMPERATURE RANGE	
RELATIVE HUMIDITY	5% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 158°F (-20° to 70°C)
TRANSMISSION RANGE	15 km
AC POWER ADAPTER INPUT SPECS (V / HZ / A)	100-240V / 50/60Hz / 1.2A
AC POWER ADAPTER OUTPUT SPECS (V / A)	5V / 2A
AC POWER ADAPTER CORD LENGTH	4.53 ft
CABLE COLOR	Black
ADAPTER	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 1.2A
HOUSING	Metal
LED INDICATORS	PWR (Power LED), L/A (Fiber port connection indicator), SD (Fiber signal indicator), SPD (Network speed), TP-L/A (Copper port connection indicator), FDX/COL (Full Duplex/Half Duplex)
DATA TRANSFER RATE	10 Mbps 100 Mbps
WAVELENGTH	1310 nm
CONNECTOR GROUP	SC RJ45
CONNECTOR	RJ45 (female) SC duplex (female)
MODE	Singlemode
NETWORK PORTS	RJ45 (FEMALE) SC (FEMALE)
OPTICAL PORT	SC
INPUT POWER SOURCE TYPE	AC Adapter
OPERATING MODE	Full/Half Duplex

