




Eaton N784-001-SC

Gigabit Multimode Fiber to Ethernet Media Converter, 10/100BaseT to 100BaseFX-SC, 2km, 1310nm

□□□□

PRODUCT NAME	Eaton Tripp Lite series media converter
CATALOG NUMBER	N784-001-SC
UPC	037332130891
PRODUCT LENGTH/DEPTH	3.7 in
PRODUCT HEIGHT	1.02 in
PRODUCT WIDTH	2.76 in
PRODUCT WEIGHT	0.47 lb
COMPLIANCES	RoHS FCC Compliant CE Marked

□□□□	
TYPE	Fiber to Ethernet
ACCESSORIES	External Power Supply (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V/2A)
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
COLOR	Black
PACKAGE CONTENTS	10/100 Multimode Media Converter, UTP - SC External Power Supply with NEMA 1-15P Plug (Input: 100-240V) Owner's Manual
IEEE STANDARDS SUPPORTED	802.3x 802.3u
CONNECTOR TYPE	Networking-copper Networking-fiber
PRODUCT FEATURES	Wavelength Division Multiplexing (WDM) Auto MDIX Support
NETWORK SPEED	10 Mbps 100 Mbps (Fast Ethernet) 10 Mbps; 100 Mbps
PRODUCT HIGHLIGHTS	Half or Full Duplex Operation Auto-Senses 10/100 2-year limited warranty (Worldwide) Convert UTP Ethernet to Fiber Supports Auto MDI/MDI-X Supports Multimode 50/125 cable up to 2KM or 62.5/125 cable up to 550M
NETWORK SPEED DETAILS	10 Mbps; 100 Mbps
PACKAGING TYPE	Box
EXTERNAL POWER SUPPLY CERTIFICATIONS	CE cUL FCC WEEE
SIDEA CONNECTOR1	RJ45 (FEMALE)
SIDEB CONNECTOR1	SC DUPLEX (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.5 x 11 mm, positive pin, negative sleeve
TECHNOLOGY	Cat5/5e Multimode
FEATURES	Flex Center
OPERATING	32° to 122°F (0° to 50°C)



TEMPERATURE RANGE	
RELATIVE HUMIDITY	5% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 158°F (-20° to 70°C)
TRANSMISSION RANGE	2 km
AC POWER ADAPTER INPUT SPECS (V / HZ / A)	100-240V / 50/60Hz / 1.2A
AC POWER ADAPTER OUTPUT SPECS (V / A)	5V / 2A
AC POWER ADAPTER CORD LENGTH	4.53 ft
CABLE COLOR	Black
ADAPTER	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 1.2A
HOUSING	Metal
LED INDICATORS	PWR (Power LED), FX LNK/ACT (Fiber port connection indicator), FX FDX/COL (Full/half duplex indicator), TP LNK/ACT (Copper port connection indicator), TP 100 (10/100 Mbps Speed Indicator)
DATA TRANSFER RATE	10 Mbps 100 Mbps
WAVELENGTH	1310 nm
CONNECTOR GROUP	RJ45 SC
CONNECTOR	RJ45 (female) SC duplex (female)
MODE	Multimode
NETWORK PORTS	RJ45 (FEMALE) SC (FEMALE)
OPTICAL PORT	SC
INPUT POWER SOURCE TYPE	AC Adapter
OPERATING MODE	Full/Half Duplex

