




Eaton N820-10M-IND

10Gb Rigid Industrial Duplex Multimode
50/125 OM3 Fiber Patch Cable (LC/LC) - IP68,
Aqua, 10 m (32.8 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N820-10M-IND
UPC	037332252753
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	1.3393 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH

□□□□	
CABLE JACKET RATING	OFNR
CABLE JACKET COLOR	Aqua
PACKAGE CONTENTS	N820-10M-IND 10Gb Duplex Multimode 50/125 OM3 Fiber Patch Cable, Aqua, 10 m
CONNECTOR COLOR	Beige
CONNECTOR TYPE	Networking-fiber
PRODUCT FEATURES	Industrial Grade
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Resists dust and endures immersion in 1.5 m of water up to 60 min. Low insertion loss of >0.10 db ensures a strong signal through your network Protects 10Gb fiber Ethernet applications in outdoor or harsh environments Color-coded aqua for fast, easy OM3 identification in a crowded rack or patch panel
SIDEA CONNECTOR1	LC DUPLEX (MALE)
SIDEB CONNECTOR1	LC DUPLEX (MALE)
TECHNOLOGY	Multimode
FEATURES	Flex Center
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
RELATIVE HUMIDITY	0-90% non-condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 140°F (-15° to 60°C)
BEND RADIUS - MIN	7.5 * 20=150mm
CLAD DIAMETER	50
CORE DIAMETER - MAX	125
INSERTION LOSS	≤ 0.10 dB
NUMBER OF FIBERS	2
OUTER CABLE DIAMETER	7.5 mm
FIBER CABLE LENGTH	10M (32.8 ft)
CONNECTOR GROUP	LC



CONNECTOR	LC duplex (male)
ATTENUATION 1310NM	1.5dB/km
ATTENUATION 850NM	3.5 dB/km
ENDFACE POLISH	PC
OPTICAL MODE	OM3
OPTICAL PORT	LC
PROTECTION RATING	
FIBER TYPE	50/125



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

