

Eaton NS10

Eaton Bussmann series low voltage british standard fuse, 10A, AC 440 V, V88/F1, 15 x 62 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	NS10
UPC	051712392518
PRODUCT LENGTH/DEPTH	62 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	16.2 g
COMPLIANCES	Contact Manufacturer

AMPERAGE RATING	10 A
CURRENT TYPE	AC
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	440 V
CLASS	Class gG/gL
FUSE TYPE	NS
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Blade end
CONSTRUCTION	BS88/F1
CONSTRUCTION SIZE	F1
FUSE SHAPE	Offset bladed tags
VOLTAGE TYPE	AC
VOLTAGE RATING	440 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:

