

Eaton NSD4

Eaton Bussmann series low voltage british standard fuse, 4A, AC 550 V, V88/F1, 14 x 59 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	NSD4
UPC	051712840347
PRODUCT LENGTH/DEPTH	58.5 mm
PRODUCT HEIGHT	13.8 mm
PRODUCT WIDTH	13.8 mm
PRODUCT WEIGHT	16.15 g
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	4 A
FITTED WITH:	Offset bladed tags
FUSE SIZE	BS88/F1
CURRENT TYPE	AC
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	550 V
CLASS	Class gG/gL
FUSE TYPE	NSD
CONTACT MATERIAL	Offset blade tag, HRC
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	1.4 W
CONNECTION	Blade end
CONSTRUCTION	BS88/F1
CONSTRUCTION SIZE	F1
FUSE SHAPE	Offset bladed tags
VOLTAGE TYPE	AC
SUITABLE FOR	32NNS Safeloc fuse holder
	SC32 Safeclip fuse holder
QUANTITY	20
VOLTAGE RATING	550 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250942en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

