



Eaton ODD160

Eaton Bussmann series low voltage british standard fuse, 160A, AC 415 V, 31 x 91 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	ODD160
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	36 mm
PRODUCT WIDTH	192 mm
PRODUCT WEIGHT	130 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

□□□□

□□

AMPERAGE RATING	160 A
CURRENT TYPE	AC
MOUNTING DIMENSION	M6
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	71.6 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	ODD
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Bolt-on
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

