



Eaton P004-002-13LA

Power Extension Cord, Left-Angle C13 to C14
PDU Style - 10A, 250V, 18 AWG, 2 ft. (0.61 m),
Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P004-002-13LA
UPC	037332156426
PRODUCT LENGTH/DEPTH	9.1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	4.9 in
PRODUCT WEIGHT	0.2 lb
COMPLIANCES	RoHS REACH
CERTIFICATIONS	CSA certified cUL Listed UL Listed

INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Printer Monitor/HDTV UPS Server Computer PDU
AWG-SIZE	18
CABLE LENGTH	2 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	7.8mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P004-002-13LA C14 Male to C13 Female Power Cable, 2-ft. (0.61 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	Angled Plug High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Angled
PRODUCT HIGHLIGHTS	Recommended for powering computers, printers and other essential peripherals Lifetime limited warranty (Worldwide) Left-angle C13 plug allows easier connection in confined or hard-to-reach spaces C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable Adds 2-ft. (0.61 m) to your existing power connection

	to provide flexibility in placing devices
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14
SIDEB CONNECTOR1	IEC-320-C13 - LEFT ANGLE
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C14 C13
CONNECTOR	IEC 320-C13 left angle IEC 320-C14

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton Ireland

Follow us on social media

