



Eaton P004-002-13RA

Power Extension Cord, Right-Angle C13 to C14 PDU Style - 10A, 250V, 18 AWG, 2 ft. (0.61 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P004-002-13RA
UPC	037332156419
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.24 lb
COMPLIANCES	RoHS REACH
CERTIFICATIONS	UL Listed CSA certified cUL Listed



Powering Business Worldwide



INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Computer Printer Monitor/HDTV Server PDU UPS
AWG-SIZE	18
CABLE LENGTH	2 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	7.8mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P004-002-13RA C14 Male to C13 Female Power Cable, 2-ft. (0.61 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage Angled Plug
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Angled
PRODUCT HIGHLIGHTS	C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable Right-angle C13 plug allows easier connection in confined or hard-to-reach spaces Recommended for powering computers, printers and other essential peripherals Adds 2-ft. (0.61 m) to your existing power connection to provide flexibility in placing devices

