



Eaton P004-002-5

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 2 ft. (0.61 m), Black, 5-Pack

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P004-002-5
UPC	037332142863
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	14.17 in
PRODUCT WIDTH	11.8 in
PRODUCT WEIGHT	1.1 lb
COMPLIANCES	RoHS REACH
CERTIFICATIONS	CSA certified cUL Listed UL Listed



Powering Business Worldwide



INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	UPS Monitor/HDTV Computer Server PDU Printer
AWG-SIZE	18
CABLE LENGTH	2 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	20% to 80% RH
OUTER CABLE DIAMETER	7.7mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	20% to 80% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	(5) C14 Male to C13 Female Power Cables, 2-ft. (0.61 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Add 2-ft. (0.61 m) to your existing connection to provide more flexibility in placing devices C13-to-C14 PDU-style extension cords are ideal replacements for worn-out or missing cable Recommended for powering computers, printers and other essential peripherals
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14
SIDEB CONNECTOR1	IEC-320-C13

