



Eaton P004-003-13A

PDU Power Cord, C13 to C14 - 13A, 250V, 16 AWG, 3 ft. (0.91 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P004-003-13A
UPC	037332180445
PRODUCT LENGTH/DEPTH	0.1 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.35 lb
COMPLIANCES	RoHS REACH
CERTIFICATIONS	UL Listed CSA certified cUL Listed

INPUT CURRENT -MAX	13 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Computer UPS Server Printer Monitor/HDTV PDU
AWG-SIZE	16
CABLE LENGTH	3 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	20% to 80% RH
OUTER CABLE DIAMETER	9mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	20% to 80% RH
WIRE SIZE (AWG) - MAX	1.31
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P004-003-13A C14 Male to C13 Female Power Cable, 3 ft., Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Adds 3-ft. (0.91 m) to your existing power connection to provide flexibility in placing devices C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable Recommended for powering computers, printers and other essential peripherals
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14

SIDE B CONNECTOR1	IEC-320-C13
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C13 C14
CONNECTOR	IEC 320-C13 IEC 320-C14
