



Eaton P004-004-BL

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 4 ft. (1.22 m), Blue

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P004-004-BL
UPC	037332173218
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.42 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	CSA certified UL Listed cUL Listed

INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Server Monitor/HDTV Computer PDU UPS Printer
AWG-SIZE	18
CABLE LENGTH	4 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	20% to 80% RH
OUTER CABLE DIAMETER	7.7mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	20% to 80% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P004-004 C14 Male to C13 Female Power Cable, 4-ft. (1.22 m), Blue
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable Lifetime limited warranty (Worldwide) 4-ft. (1.22 m) length allows flexibility in placing devices, while avoiding cable clutter Color-coded blue for fast, easy identification in a crowded rack or workstation Recommended for powering computers, printers and other

	essential peripherals
PLUG COLOR	Blue
SIDEA CONNECTOR1	IEC-320-C14
SIDEB CONNECTOR1	IEC-320-C13
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C14 C13
CONNECTOR	IEC 320-C14 IEC 320-C13

□□□□:
□□□□:
□□□:
□□: