



Eaton P004-004-GN

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 4 ft. (1.22 m), Green

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P004-004-GN
UPC	037332168337
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.42 lb
COMPLIANCES	RoHS REACH
CERTIFICATIONS	UL Listed cUL Listed CSA certified

OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
-----------------------------	-----------------------------

STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
---------------------	-----------------------------

DEVICE COMPATIBILITY	UPS Computer Monitor/HDTV Printer Server PDU
----------------------	---

AWG-SIZE	18
----------	----

CABLE LENGTH	4 Foot
--------------	--------

NUMBER OF CONDUCTORS	3
----------------------	---

OPERATING HUMIDITY	20% to 80% RH
--------------------	---------------

OUTER CABLE DIAMETER	7.7mm
----------------------	-------

POWER CORD JACKET TYPE	SJT
------------------------	-----

STORAGE HUMIDITY RANGE	20% to 80% RH
------------------------	---------------

WIRE SIZE (AWG) - MAX	0.82
-----------------------	------

CABLE LENGTH RANGE	Up to 4ft (up to 1M)
--------------------	----------------------

CABLE JACKET RATING	FT2
---------------------	-----

CABLE JACKET COLOR	Black
--------------------	-------

PACKAGE CONTENTS	P004-004 C14 Male to C13 Female Power Cable, 4-ft. (1.22 m), Green
------------------	--

CONNECTOR TYPE	Power
----------------	-------

PRODUCT FEATURES	High Voltage
------------------	--------------

CABLE JACKET MATERIAL	PVC
-----------------------	-----

PRODUCT HIGHLIGHTS	4-ft. (1.22 m) length allows flexibility in placing devices, while avoiding cable clutter C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable Color-coded green for fast, easy identification in a crowded rack or workstation Recommended for powering computers, printers and other essential peripherals
--------------------	---

PLUG COLOR	Green
------------	-------

SIDEA CONNECTOR1	IEC-320-C14
------------------	-------------

SIDEB CONNECTOR1	IEC-320-C13
------------------	-------------

VOLTAGE RATING	100 - 250 VAC
----------------	---------------

CONNECTOR GROUP	C14 C13
CONNECTOR	IEC 320-C14 IEC 320-C13
