



Eaton P004-006-13A

PDU Power Cord, C13 to C14 - 13A, 250V, 16 AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P004-006-13A
UPC	037332180407
PRODUCT LENGTH/DEPTH	0.1 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.57 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	CSA certified cUL Listed UL Listed

INPUT CURRENT -MAX	13 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Printer Monitor/HDTV Server PDU Computer UPS
AWG-SIZE	16
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	20% to 80% RH
OUTER CABLE DIAMETER	9mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	20% to 80% RH
WIRE SIZE (AWG) - MAX	1.31
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P004-006-13A C14 Male to C13 Female Power Cable, 6-ft. (1.83 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Adds 6-ft. (1.83 m) to your existing power connection to provide flexibility in placing devices Recommended for powering computers, printers and other essential peripherals C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable Lifetime limited warranty (Worldwide)
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14

SIDE B CONNECTOR1	IEC-320-C13
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C14 C13
CONNECTOR	IEC 320-C14 IEC 320-C13
