



Eaton P004-006-2C13

C14 Male to C13 Female Splitter, PDU Style - C14 to 2x C13, 10A, 250V, 18 AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series splitter
CATALOG NUMBER	P004-006-2C13
UPC	037332154750
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.73 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	cUL Listed CSA certified UL Listed

INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Printer PDU Computer Scanner Monitor/HDTV UPS
AWG-SIZE	18
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	7.8mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P004-006-2C13 C14 Male to C13 Female Splitter, PDU Style, 6-ft. (1.83 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet Lifetime limited warranty (Worldwide) Ideal replacement for worn-out or missing C13-to-C14 PDU-style extension cord Connects 2 devices to one AC outlet to save space and reduce cable clutter Recommended for powering dual computers, monitors or other

	compatible peripherals
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14
SIDEB CONNECTOR1	IEC-320-C13
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C14 C13
CONNECTOR	IEC 320-C13 IEC 320-C14



Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

