



## Eaton P004-006

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 6 ft. (1.83 m), Black



<b>PRODUCT NAME</b>	Eaton Tripp Lite series PDU power cord
<b>CATALOG NUMBER</b>	P004-006
<b>UPC</b>	037332013378
<b>PRODUCT LENGTH/DEPTH</b>	11 in
<b>PRODUCT HEIGHT</b>	0.6 in
<b>PRODUCT WIDTH</b>	7 in
<b>PRODUCT WEIGHT</b>	0.53 lb
<b>COMPLIANCES</b>	REACH RoHS
<b>CERTIFICATIONS</b>	cUL Listed UL Listed CSA certified



Powering Business Worldwide



<b>INPUT CURRENT -MAX</b>	10 Ampere
<b>OPERATING TEMPERATURE RANGE</b>	-4° to 140°F (-20° to 60°C)
<b>STORAGE TEMPERATURE</b>	-4° to 140°F (-20° to 60°C)
<b>DEVICE COMPATIBILITY</b>	Server UPS Printer Computer Monitor/HDTV PDU
<b>AWG-SIZE</b>	18
<b>CABLE LENGTH</b>	6 Foot
<b>NUMBER OF CONDUCTORS</b>	3
<b>OPERATING HUMIDITY</b>	10% to 65% RH
<b>OUTER CABLE DIAMETER</b>	7.8mm
<b>POWER CORD JACKET TYPE</b>	SJT
<b>STORAGE HUMIDITY RANGE</b>	10% to 65% RH
<b>WIRE SIZE (AWG) - MAX</b>	0.82
<b>CABLE LENGTH RANGE</b>	5 - 8ft (1 - 2M)
<b>CABLE JACKET RATING</b>	VW-1
<b>CABLE JACKET COLOR</b>	Black
<b>PACKAGE CONTENTS</b>	P004-006 C14 Male to C13 Female Power Cable, 6-ft. (1.83 m), Black
<b>CONNECTOR COLOR</b>	Black
<b>CONNECTOR TYPE</b>	Power
<b>PRODUCT FEATURES</b>	High Voltage
<b>CABLE JACKET MATERIAL</b>	PVC
<b>CONNECTOR STYLE</b>	Straight
<b>PRODUCT HIGHLIGHTS</b>	Recommended for powering computers, printers and other essential peripherals C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable Adds 6-ft. (1.83 m) to your existing power connection to provide flexibility in placing devices
<b>PLUG COLOR</b>	Black
<b>SIDEA CONNECTOR1</b>	IEC-320-C14
<b>SIDEB CONNECTOR1</b>	IEC-320-C13

