



Eaton P004-010

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 10 ft. (3.05 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P004-010
UPC	037332164759
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.68 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	UL Listed CSA certified cUL Listed



Powering Business Worldwide



INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	UPS Server Computer Monitor/HDTV PDU Printer
AWG-SIZE	18
CABLE LENGTH	10 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	7.8mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P004-010 C14 Male to C13 Female Power Cable, 10-ft. (3.05 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Recommended for powering computers, printers and other essential peripherals C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable Adds 10-ft. (3.05 m) to your existing power connection to provide flexibility in placing devices
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14
SIDEB CONNECTOR1	IEC-320-C13

