



Eaton P005-002

Heavy-Duty PDU Power Cord, C13 to C14 -
15A, 250V, 14 AWG, 2 ft. (0.61 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P005-002
UPC	037332149992
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.33 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	UL Listed cUL Listed CSA certified

PDU Power Cord		PDU Power Cord	
TYPE	PDU Power Cord		
INPUT CURRENT -MAX	15 Ampere		
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)		
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)		
DEVICE COMPATIBILITY	Router Monitor/HDTV Printer PDU Server Computer UPS Network Switch		
AWG-SIZE	14		
CABLE LENGTH	2 Foot		
NUMBER OF CONDUCTORS	3		
OPERATING HUMIDITY	10% to 65% RH		
OUTER CABLE DIAMETER	9.3mm		
POWER CORD JACKET TYPE	SJT		
STORAGE HUMIDITY RANGE	10% to 65% RH		
WIRE SIZE (AWG) - MAX	2.08		
CABLE LENGTH RANGE	Up to 4ft (up to 1M)		
CABLE JACKET RATING	VW-1		
CABLE JACKET COLOR	Black		
PACKAGE CONTENTS	P005-002 Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 2-ft. (0.61 m), Black		
CONNECTOR COLOR	Black		
CONNECTOR TYPE	Power		
PRODUCT FEATURES	High Voltage		
CABLE JACKET MATERIAL	PVC		
CONNECTOR STYLE	Straight		
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) PDU-style cord replaces or upgrades standard power cord provided by manufacturer Recommended for powering computers, servers and other network devices 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding		

	cable clutter Thick 14 AWG wire gauge manages high power levels required for larger equipment
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14
SIDEB CONNECTOR1	IEC-320-C13
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C14 C13
CONNECTOR	IEC 320-C13 IEC 320-C14
