



Eaton P005-006-14LA

Heavy-Duty PDU Power Cord, C13 to Left-Angle C14 - 15A, 250V, 14 AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P005-006-14LA
UPC	037332179920
PRODUCT LENGTH/DEPTH	0.1 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.66 lb
COMPLIANCES	RoHS REACH
CERTIFICATIONS	CSA certified UL Listed cUL Listed

INPUT CURRENT -MAX	15 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Router Monitor/HDTV Printer Server Network Switch UPS Computer PDU
AWG-SIZE	14
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	20% to 80% RH
OUTER CABLE DIAMETER	9.2mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	20% to 80% RH
WIRE SIZE (AWG) - MAX	2.08
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P005-006-14LA C13 to Left-Angle C14 Power Cable, 6-ft. (1.83 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	Angled Plug High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Angled
PRODUCT HIGHLIGHTS	Recommended for powering computers, servers and other network devices Thick 14 AWG wire gauge manages high power levels required for larger equipment Left-angle C14 plug allows easier connection in confined or hard-to-reach spaces PDU-style cord replaces or upgrades standard power

	cord provided by manufacturer Lifetime limited warranty (Worldwide) 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14 - LEFT ANGLE
SIDEB CONNECTOR1	IEC-320-C13
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C13 C14
CONNECTOR	IEC 320-C14 left angle IEC 320-C13
