



## Eaton P005-006-YW

Heavy-Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 6 ft. (1.83 m), Yellow Plugs

□□□□

<b>PRODUCT NAME</b>	Eaton Tripp Lite series PDU power cord
<b>CATALOG NUMBER</b>	P005-006-YW
<b>UPC</b>	037332168382
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	9 in
<b>PRODUCT WIDTH</b>	7 in
<b>PRODUCT WEIGHT</b>	0.68 lb
<b>COMPLIANCES</b>	REACH RoHS
<b>CERTIFICATIONS</b>	cUL Listed UL Listed CSA certified



Powering Business Worldwide



<b>INPUT CURRENT -MAX</b>	15 Ampere
<b>OPERATING TEMPERATURE RANGE</b>	-4° to 140°F (-20° to 60°C)
<b>STORAGE TEMPERATURE</b>	-4° to 140°F (-20° to 60°C)
<b>DEVICE COMPATIBILITY</b>	Router Computer UPS Printer Monitor/HDTV Server Network Switch PDU
<b>AWG-SIZE</b>	14
<b>CABLE LENGTH</b>	6 Foot
<b>NUMBER OF CONDUCTORS</b>	3
<b>OPERATING HUMIDITY</b>	20% to 80% RH
<b>OUTER CABLE DIAMETER</b>	9.2mm
<b>POWER CORD JACKET TYPE</b>	SJT
<b>STORAGE HUMIDITY RANGE</b>	20% to 80% RH
<b>WIRE SIZE (AWG) - MAX</b>	2.08
<b>CABLE LENGTH RANGE</b>	5 - 8ft (1 - 2M)
<b>CABLE JACKET RATING</b>	FT2
<b>CABLE JACKET COLOR</b>	Black
<b>PACKAGE CONTENTS</b>	P005-006-YW Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 6- ft. (1.83 m), Yellow Plugs
<b>CONNECTOR COLOR</b>	Yellow
<b>CONNECTOR TYPE</b>	Power
<b>PRODUCT FEATURES</b>	High Voltage
<b>CABLE JACKET MATERIAL</b>	PVC
<b>CONNECTOR STYLE</b>	Straight
<b>PRODUCT HIGHLIGHTS</b>	Thick 14 AWG wire gauge manages high power levels required for larger equipment Recommended for powering computers, servers and other network devices PDU-style cord replaces or upgrades standard power cord provided by manufacturer Color-coded yellow ends for fast, easy identification



